PMD AND CD ANALYZERS

FTB-5500B/FTB-5800



Polarization Mode Dispersion Analyzer-FTB-5500B

- Less than five-second testing time for any PMD range
- No auto-correlation peak, for enhanced accuracy
- NIST traceable
- Ideal for aerial fibers
- Patented design*: test through EDFAs
- = 100 Gbit/s-ready

Chromatic Dispersion Analyzer-FTB-5800**

Protected by US patent 7,227,645 and equivalents in several other countries. Measurement method approved

- Complete CD characterization
- Highly accurate phase-shift method
- No communication between source and receiver
- Patented design*: test through EDFAs
- = 100 Gbit/s-ready

Platform Compatibility

** Protected by US patent 6,429,929 and foreign equivalents.

FTB-500 Platform

by TIA-FOTP-124A.





SHARE LEADERSHIP AWARD

Next-Generation Network Assessment





Combining CD and PMD for Precise Link Characterization

Designed for ultra-long-haul and 40 Gbit/s applications, EXFO's FTB-5500B PMD and FTB-5800 CD analyzer combo provides you with the speed, accuracy and high performance you need to ensure high-quality network services. Housed in the expert FTB-500 Platform, the FTB-5500B and FTB-5500 test modules survive splashes, knocks and drops-ideal for CO and field conditions.



EXFO's CD and PMD analyzers, housed in the FTB-500 platform

Measuring Polarization Mode Dispersion the Fast Way

Polarization mode dispersion (PMD) represents a significant danger to both legacy and newly deployed networks. And as systems of 10 Gbit/s and faster develop, PMD concern and awareness continue to grow. EXFO's FTB-5500B PMD Analyzer helps you get ahead in the field. Whether you need to verify the capacity of legacy fiber or upgrade a network to any speed, the modular FTB-5500B is fast, reliable and ready to go.



FTB-5500B PMD Analyzer

Key Features	Key Benefits
Five-second testing time	Test more fiber, faster
No auto-correlation peak	Ultra-high accuracy
Testing through EDFAs	Reduce test cost
Suitable for all networks	Future-proof: 100 Gbit/s-ready, designed for long-haul and ultra-long-haul networks

Second-Order PMD


Particularly important in multichannel transmission and as rates reach 40 Gbit/s and higher, second-order PMD is derived from the measured PMD value. EXFO's software provides second-order PMD delay and coefficient values for telecom fibers. These values allow you to characterize fibers and cables more precisely than simple PMD and better control the transmission quality of high-speed systems.

Characterizing Chromatic Dispersion in the Field

The ongoing race to develop high-speed transmission systems and to increase available bandwidth is facing certain limitations. Chromatic dispersion (CD) measurements are becoming more and more critical for carriers and service providers looking to improve their systems by upgrading to extreme speed. EXFO's FTB-5800 CD Analyzer offers high performance in a field-ready unit for all chromatic dispersion testing situations.



FTB-5800 CD Analyzer




Powerful Software Features at the Touch of a Button

EXFO's ToolBox software suite runs the FTB-500's test module applications. The user-friendly touchscreen provides easy access to menus and functions, for highly productive, yet simple testing in the field.

Set and test.


Simple test setup parameters for error-free testing.




FTB-5800 CD Analyzer

Powerful Software Features at the Touch of a Button (Cont'd)

Personalized data management for clear, customized report creation.



Large graphic display of both the dispersion and the relative group delay.




Additional PMD and CD Combo Advantages

The Ultra-Long-Haul Advantage

Now you can test whole links instead of only sections, reducing manipulation, error and testing time. Because filtering is done at the receiver end and not at the source, transmission through one-way devices such as isolators and EDFAs is possible. Tests have been performed through as many as 250 cascaded amplifiers over a link length of more than 12 000 km.

The FLS-5800 CD/PMD Analyzer Source Advantage

A single light source, the FLS-5800 CD/PMD Analyzer Source, can help you characterize CD and PMD-reducing testing time and minimizing the potential for human error.



Fast-Track Data Post-Processing with FastReporter Software

The optional FastReporter software package provides you with the post-processing tools and functionalities you need to optimize your test cycles, whatever the application. Designed for off-line analysis of fieldacquired data, FastReporter offers a truly intuitive graphical user interface, which contributes to boosting productivity.

Flexible Reporting

Choose from various report templates, including PMD, CD and fiber characterization. Generate comprehensive cable reports in PDF, Excel or HTML format.

FTB-5500B PMD Analyzer

1260 to 1675 (O to U band)
0 to 115
-45
4.5 (for any PMD value)
± (0.020 + 2 % of PMD)
Yes (above 120 EDFAs)

Notes

a. Typical, for C band. May be increased with averaging. With the FLS-5800, the typical dynamic range is 47 dB.

b. For C band, assuming averaging over all states of polarization.

GENERAL SPECIFICATIONS			
Temperature			
operating	0 °C to 40 °C	(32 °F to 104 °F)	
storage	−40 °C to 70 °C	(–40 °F to 158 °F)	
Relative humidity	0 % to 93 % non-condensing		
Size (H x W x D) (module only)	9.6 cm x 7.6 cm x 26.0 cm	(3 ³ /4 in x 3 in x 10 ¹ /4 in)	
Weight (module only)	1.5 kg (3.4 lb)		
	-		

FTB-5800 CD Analyzer

SPECIFICATIONS ^a						
Wavelength range (nm)		1530 to 1625				
		1200 to 1700 b				
Wavelength step (nm)	Wavelength step (nm) Minimum		0.1			
Measurement points	Maximum	950, user-definable				
Dynamic range ^c (dB)		42				
Wavelength uncertainty ^d (accuracy) (nm)		0.1				
Dispersion uncertainty ^d (accuracy) (ps/nm)	20 km of G.652	1.6				
	120 km of G.652	3.1				
	20 km of G.655	1.9 (guaranteed)				
		20 km	80 km	120 km		
Dispersion repeatability ^d (ps/nm)		0.04	0.2	1.1		
Zero-dispersion wavelength λ_0 repeatability ^d (nm)		0.1	0.14	0.8		
Dispersion slope repeatability $\lambda_0 d$ (%)		0.03	0.05	0.25		
Minimum fiber length (km)		<1				
Maximum fiber length ^e (km)		> 5400				
Measurement time per point ^e (s) Minimum		< 1				

Notes

a. All specifications are typical with four seconds averaging time per point (where applicable), at a temperature of 23 °C ± 1 °C, with FC connectors and after warmup time.

b. Displayed range. Values may be extrapolated.

c. Dynamic range is defined as the difference between the strongest signal and the weakest signal the receiver can detect. Extra averaging may be required.

Uncertainty (accuracy) is not guaranteed at limits of range.

d. C+L band.

e. Including EDFAs.

f. Additional gain setting time may be required prior to the first point of each band.

GENERAL SPECIFICATIONS			
Size (H x W x D) (module)	9.6 cm x 10 cm x 26 cm	(3 ³ /4 in x 3 ¹⁵ /16 in x 10 ¹ /4 in)	
Weight (module)	2 kg	(4.5 lb)	

ORDERING INFORMATION

PMD ANALYZER

FTB-5500B-XX

Connector * EI-EUI-28 = UPC/DIN 47256 EI-EUI-76 = UPC/HMS-10/AG EI-EUI-89 = UPC/FC narrow key EI-EUI-90 = UPC/ST EI-EUI-91 = UPC/SC

Example: FTB-5500B-EI-EUI-89

FLS-5834A-XX

EI-EUI-28 = UPC/DIN 47256

EI-EUI-90 = UPC/ST (EI only)

EA-EUI-28 = APC/DIN 47256EA-EUI-89 = APC/FC narrow key

EI-EUI-91 = UPC/SC

EA-EUI-91 = APC/SC

EA-EUI-95 = APC/E-2000

EI-EUI-95 = UPC/E-2000

EI-EUI-89 = UPC/FC narrow key

Model

Connector

CD/PMD ANALYZER SOURCE

FLS-5834A = 1550 nm and 1625 nm

EI-EUI-76 = UPC/HMS-10/AG (EI only)


EI-EUI-95 = UPC/E-2000 EA-EUI-28 = APC/DIN 47256 EA-EUI-89 = APC/FC narrow key EA-EUI-91 = APC/SC EA-EUI-95 = APC/E-2000

CD ANALYZER

FTB-5800-XX

Connector ■ EI-EUI-28 = UPC/DIN 47256 EI-EUI-76 = UPC/HMS-10/AG EI-EUI-89 = UPC/FC narrow key EI-EUI-90 = UPC/SC EI-EUI-95 = UPC/SC EI-EUI-95 = UPC/E-2000 Example: FTB-5800-EI-EUI-89 EA-EUI-28 = APC/DIN 47256 EA-EUI-89 = APC/FC narrow key EA-EUI-91 = APC/SC EA-EUI-95 = APC/E-2000

POLARIZED LIGHT SOURCE (PMD TESTING ONLY)



Example: FLS-5834A-EI-EUI-89

* EXFO Universal Interface is protected by US patent 6,612,750.

SAFETY		
FLS-110	THIS PRODUCT COMPLIES WITH 21 CFR 1040.10 AND 1040.11, AND WITH IEC 60825-1:1993+A1:1997.	CLASS 1 LED PRODUCT
FLS-5834A	IEC 60825-1:2001	CLASS 1M LED PRODUCT

EXFO Corporate Headquarters > 400 Godin Avenue, Quebec City (Quebec) G1M 2K2 CANADA | Tel.: +1 418 683-0211 | Fax: +1 418 683-2170 | info@EXFO.com

			Toll-free: +1 800 663-3936 (US	Toll-free: +1 800 663-3936 (USA and Canada) www.EXFO.com	
EXFO America	3701 Plano Parkway, Suite 160	Plano, TX 75075 USA	Tel.: +1 800 663-3936	Fax: +1 972 836-0164	
EXFO Asia	100 Beach Road, #22-01/03 Shaw Tower	SINGAPORE 189702	Tel.: +65 6333 8241	Fax: +65 6333 8242	
EXFO China	36 North, 3 rd Ring Road East, Dongcheng District Room 1207, Tower C, Global Trade Center	Beijing 100013 P. R. CHINA	Tel.: + 86 10 5825 7755	Fax: +86 10 5825 7722	
EXFO Europe	Omega Enterprise Park, Electron Way	Chandlers Ford, Hampshire S053 4SE ENGLAND	Tel.: +44 2380 246810	Fax: +44 2380 246801	
EXFO NetHawk	Elektroniikkatie 2	FI-90590 Oulu, FINLAND	Tel.: +358 (0)403 010 300	Fax: +358 (0)8 564 5203	
EXFO Service Assurance	270 Billerica Road	Chelmsford, MA 01824 USA	Tel.: +1 978 367-5600	Fax: +1 978 367-5700	

EXFO is certified ISO 9001 and attests to the quality of these products. This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. EXFO has made every effort to ensure that the information contained in this specification sheet is accurate. However, we accept no responsibility for any errors or omissions, and we reserve the right to modify design, characteristics and products at any time without obligation. Units of measurement in this document conform to SI standards and practices. In addition, all of EXFO's manufactured products are compliant with the European Union's WEEE directive. For more information, please visit www.EXFO.com/recycle. Contact EXFO for prices and availability or to obtain the phone number of your local EXFO distributor. For the most recent version of this spec sheet, please go to the EXFO website at http://www.EXFO.com/specs

CE

Printed in Canada 11/04

In case of discrepancy, the Web version takes precedence over any printed literature.

